

**Key Features:**

- Single CoaXPress link support
- Multi-stream support
- Camera controls and triggers
- Per-link LED indication on card bracket
- Flexible machine I/O:
  - 4 TTL configurable I/Os
  - 4 LVCMOS configurable I/Os
  - 1 LVDS inputs
  - 1 LVDS outputs
  - 4 opto-isolated outputs
  - 4 opto-isolated inputs
  - 4 quadrature rotary encoders
  - Integrated strobe controller
  - 4 timers
- CoaXPress V1.1 compliant
- Power over CoaXPress with 13W per link
- Multiple Frame Grabbers synchronization
- DIN 1.0/2.3 or Micro-BNC connectors for CoaXPress links
- GUI interface
- CoaXPress drivers for loopback function
- Supporting Windows and Linux OS
- API for developing custom applications
- Plug-ins modules for Matlab, HALCON and Labview
- Gen<i>Cam compliant
- GenTL support
- 4 Gb image buffer
- PCIe Gen2 x4 Low profile PCIe card
- Full or Half-height bracket
- Data rates up to 6.25 Gbps per link
- 0°C to 50°C operating environment

## Predator Frame Grabber

**Innovative**


Predator is a low-cost Frame Grabber supporting CoaXPress standard. The Predator is capable of receiving video streams from a single CoaXPress link. The Frame Grabber supports standard CoaXPress bitrates up to 6.25 Gbps including PoCXP. This CoaXPress frame grabber is ideally suited for industrial, defense and aerospace Machine Vision Systems applications.

**Intelligent Design**

The Predator can easily receive video streams on the CoaXPress links and transmit them to computer memory through the PCIe interface. This product also provides GPIO for machine control signals such as triggers, shaft encoders, exposure control and general I/O, which can be controlled aside the video stream acquisition.

The Predator uses standard DIN connectors as a CoaXPress interface to the camera and standard 100 mil headers for general purpose I/O. The frame grabber utilizes PCIe Gen2 x4 links for communication with Host PC for video uploading and configuration.

## Datasheet | Predator™ Single Channel – CoaXPress Frame Grabber



Product Name	Predator™ 1 Channel – CoaXPress Frame Grabber
Form Factor	PCI Express card
Format	Low profile, half length, 4-lane PCI Express card
Cooling method	Air cooling, passive heatsink
Mounting	For insertion in a low profile, 4-lane or higher, PCI Express card slot
Connectors	1x DIN 1.0/2.3 female or Micro-BNC connectors CoaXPress host interface Internal I/O connector 1 on PCB 26-pin 2-row 0.1" pitch pin header with shrouding for I/O lines Auxiliary power input (PoCXP) on PCB 6-pin PEG power socket 12 VDC power input for PoCXP camera(s)
Dimensions	L 167.65 mm x H 68.9 mm L 6.6 in x H 2.71 in
Weight	130gr
Host bus	
Standard	PCI Express 2.0
Link width	4 lanes 1 lane with reduced performance
Link speed	12.5 Gbps (PCIe 2.0)
Maximum payload size	512 bytes
DMA	<ul style="list-style-type: none"><li>• 32- and 64-bit</li><li>• Scatter gather support</li><li>• Physical address support (GPU transfers)</li></ul>
Peak delivery bandwidth	2,000 MB/s
Effective (sustained), delivery bandwidth	1,700 MB/s (Host PC motherboard dependent)
Power consumption	Typ. 7 W , excluding camera and I/O power output


<b>Camera / video inputs</b>	
Interface standard(s)	CoaXPress 1.0 and 1.1
Connectors	1x DIN1.0/2.3 CXP-6 or Micro-BNC
Status LEDs	1 CoaXPress Host connection status per connector 4 System status LEDs
Number of cameras	1
Number of links, per single camera	1
Line-scan cameras supported	Yes
<b>Supported CXP down-connection speeds</b>	<ul style="list-style-type: none"> <li>• 1.25 GT/s (CXP-1)</li> <li>• 2.5 GT/s (CXP-2)</li> <li>• 3.125 GT/s (CXP-3)</li> <li>• 5 GT/s (CXP-5)</li> <li>• 6.25 GT/s (CXP-6)</li> </ul>
<b>Supported CLHS speeds</b>	
Number of data streams (per camera)	1 data stream per camera
Maximum stream packet size	8,192 bytes
PoCXP (Power over CoaXPress)	<ul style="list-style-type: none"> <li>• PoCXP Safe Power</li> <li>• 13 W of 24V DC regulated power per CoaXPress connector</li> <li>• PoCXP Device detection and automatic power-on</li> <li>• Overload and short-circuit protections</li> <li>• On-board 12V to 24V DC/DC converter</li> <li>• A +12V power source must be connected to the auxiliary power input connector</li> </ul>
Camera types	<ul style="list-style-type: none"> <li>• Area-scan cameras:</li> <li>• Gray-scale and color (RGB and Bayer CFA)</li> <li>• Single-tap (1X-1Y) progressive-scan</li> <li>• Line-scan cameras</li> <li>• Gray-scale and color RGB</li> </ul>
Camera pixel formats supported	Raw, Monochrome, Bayer, RGB, YUV, YCbCr and RGBA (PFNC names): <ul style="list-style-type: none"> <li>• Raw</li> <li>• Mono8, Mono10, Mono12, Mono14, Mono16</li> <li>• BayerXX8, BayerXX10, BayerXX12, BayerXX14, BayerXX16 where XX = GR, RG, GB, or BG</li> <li>• RGB8, RGB10, RGB12, RGB14, RGB16</li> <li>• RGBA8, RGBA10, RGBA12, RGBA14, RGBA16</li> <li>• YUV411_8, YUV411_10, YUV411_12, YUV411_14, YUV411_16</li> <li>• YUV422_8, YUV422_10, YUV422_12, YUV422_14, YUV422_16</li> <li>• YUV444_8, YUV444_10, YUV444_12, YUV444_14, YUV444_16</li> <li>• YCbCr601_411_8, YCbCr601_411_10, YCbCr601_411_12, YCbCr601_411_14, YCbCr601_411_16</li> <li>• YCbCr601_422_8, YCbCr601_422_10, YCbCr601_422_12, YCbCr601_422_14, YCbCr601_422_16</li> <li>• YCbCr601_444_8, YCbCr601_444_10, YCbCr601_444_12, YCbCr601_444_14, YCbCr601_444_16</li> </ul>
<b>Area-scan camera control</b>	
Trigger	Precise control of asynchronous reset cameras, with exposure control Support of camera exposure/readout overlap Support of triggering from encoder or timer Support of external hardware trigger, with optional delay, filtering and trigger decimation
Strobe	Accurate control of the strobe position for strobe light sources Support of early and late strobe pulses
<b>Line-scan camera control</b>	
Scan/page trigger	Precise control of start-of-scan and end-of-scan triggers Support of external hardware trigger, with optional delay and filtering Support of triggering from encoder Support of infinite acquisition, without missing lines

Line trigger	Support for quadrature motion encoders, with programmable filters, selection of acquisition direction and backward motion compensation
Line strobe	Accurate control of the strobe position for strobe light sources
<b>On-board processing</b>	
On-board memory	4 Gb
Decimation	Line skip
Additional features	Unpacking of 10-/12-/14-bit to 16-bit with justification to LSb
Frame Timestamp	64bit with 8ns precision
Data stream statistics	Measurement of: <ul style="list-style-type: none"> <li>• Frame/Line rate</li> <li>• CRC Errors</li> <li>• Dropped frames</li> <li>• Received packets</li> <li>• Test packets</li> </ul>
Event signaling and counting	The application software can be notified of the occurrence of various events: <ul style="list-style-type: none"> <li>• Newly acquired buffers</li> <li>• Camera and Illumination control events</li> <li>• I/O events</li> <li>• Timer events</li> <li>• Encoder events</li> </ul>
<b>General Purpose Inputs and Outputs</b>	
Number of lines	20 I/O lines: <ul style="list-style-type: none"> <li>1 differential inputs</li> <li>1 differential outputs</li> <li>4 singled-ended TTL inputs/outputs</li> <li>4 singled-ended LVCTTL inputs/outputs</li> <li>4 opto-isolated inputs</li> <li>4 opto-isolated outputs</li> </ul>
Usage	Any System I/O input lines can be connected to any I/O line Any I/O line can be used to decode A/B and Z signals of a motion encoder Any I/O line can generate any trigger event Any I/O line can trigger a timer
Electrical specifications	Differential lines - LVDS compatible TTL lines - 5V TTL compliant LVTTTL lines - 3.3V LVTTTL compliant Isolated lines - opto isolated lines with voltage range up to 30V
Filter control	Glitch removal filter available on all System I/O input lines Configurable filter time constants: for DIN and TTLIO lines: 50 ns, 100 ns, 200 ns, 500 ns, 1 $\mu$ s for IIN lines: 500 ns, 1 $\mu$ s, 2 $\mu$ s, 5 $\mu$ s, 10 $\mu$ s
Polarity control	Yes
Encoders	8 quadrature encoders with A/B and Z inputs 32bit position counter Forward and backward counting Position trigger support Noise filtering
Timers	8 general purpose timers Configurable delay and duration 32bit accumulator
Event reporting	64 bit system timestamp event reporting Each I/O line can generate event on configurable edge Each Timer can generate event Each encoder can generate event
<b>Frame grabber synchronization</b>	
Synchronization	Precise area and line-scan cameras synchronization across different frame grabbers



Software	
Host PC Operating System	Microsoft Windows 7/10 32- and 64-bit versions, Linux open source driver compatible with a wide range of distributions, tested and precompiled for Ubuntu 14.04 , RedHat 6.5 , CentOS 7 32- and 64-bit versions
Buffer management	Circular buffer support Accumulation of several frames/lines to single buffer to reduce CPU load DMA Buffer filling directly to system memory
GUI	Supported for Windows and Linux OS Multi-camera display and configuration Flexible buffer queuing Image/video recording
Debugging capabilities	Event logging Statistics counters
Gen<i>Cam	Support of Gen<i>Cam up to 2.4 Full camera and frame grabber parameters configuration
Environmental conditions	
Operating ambient air temperature	0°C to +50°C / +32°F to +122 °F
Operating ambient air humidity	10% to 90% RH non-condensing
Storage ambient air temperature	-20°C to +70°C / -4°F to +158°F
Storage ambient air humidity	10% to 90% RH non-condensing
Certifications	
Electromagnetic - EMC standards	The European Council EMC Directive 2004/108/EC The Unites States FCC rule 47 CFR 15
EMC - Emission	EN 55022:2010 Class B FCC 47 Part 15 Class B
EMC - Immunity	EN 55024:2010 Class B EN 61000-4-3, EN 61000-4-4, EN 61000-4-6
Flammability	PCB compliant with UL 94 V-0
RoHS	Compliant with the European Union Directive 2011/65/EU (ROHS2)
REACH	Compliant with the European Union Regulation No 1907/2006
WEEE	Must be disposed of separately from normal household waste and must be recycled according to local regulations
Ordering Information	
Optional accessories	GPIO Expansion bracket

## Predator Frame Grabber HW Block Diagram



## Compatibility

### Supported vision standard



### Supported operating systems



### Supported vision libraries



Compatible with the most of the popular machine vision libraries.

KAYA Instrument strives to create and maintain compatibility and interfaces for the most common and advanced vision image processing libraries and applications. Major support is available for **MVTec Halcon**, **National Instruments LabVIEW** and **MathWorks MATLAB**. Please check our KAYA website for an up-to-date list of other supported libraries and software package.

## Contact



Please visit [www.kayainstruments.com](http://www.kayainstruments.com) for complete product information.

Get in touch with our team at [info@kayainstruments.com](mailto:info@kayainstruments.com).

We would be glad to assist you with our state-of-the-art products and solutions. Please note, we can cover specific requirements and provide customization as well.

Worldwide

### KAYA Instruments

20 HaMesila St. Neshet  
3688520 POB 25004,  
Haifa 3125001 Israel

[info@kayainstruments.com](mailto:info@kayainstruments.com)

Tel: +972 72 272 3500

Fax: +972 72 272 3511

The information provided here is subject to change without prior notice.



<http://www.kayainstruments.com/products/frame-grabbers/>

© 2017 KAYA Instruments, Inc. All rights reserved. KAYA Instruments, the KAYA Instruments Komodo logo, JetCam logo, Predator and combinations thereof are trademarks of KAYA Instruments, Inc. in the United States and/or other jurisdictions. Microsoft Windows is a registered trademark of Microsoft Corporation. Other names are for informational purposes only and may be trademarks of their respective owners. KAYA Instruments is not liable for harm or damage incurred by information contained in this document. PID 04122017\_1KY-FGP-100